

ETHICON

ETHIBOND* *EXCEL*

Polybutylate Coated
Braided Polyester Suture



ETHIBOND* *EXCEL*

Polybutylate Coated Braided Polyester Suture

Braided

For easy handling and secure knot tying.

Non-Absorbable

Provides permanent tensile strength retention in tissue.

Soft and Pliable

For excellent knot security.

Coated

With Polybutylate for smooth tie down and easy passage through tissue.

Synthetic

Elicits only minimal tissue reaction.

Colour

Green or white.

Range

Gauge sizes 7-0 to 5 (U.S.P.). Supplied as needled sutures and ligatures.



Sterilisation








By Irradiation, except those products with pledgets which are sterilised by Ethylene Oxide.


These sutures comply with the requirements of U.S. Pharmacopoeia (U.S.P.) and The European Pharmacopoeia (PhEUR).

ETHIBOND* *EXCEL*

Polybutylate Coated Braided Polyester Suture










Needle length and description		Length	Colour	Gauge						
⊙ 3/8 circle Taper Point				6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
	BV	11mm	75cm	green	W6597					
	C-1	13mm	75cm	green		W6890	W6891			

⊙ 1/2 circle Taper Point				6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
	RB-1	17mm	60cm	green		W6757		W6759		
	RB-1	17mm	90cm	green				W6760		
	SH-2	20mm	75cm	green			W6761		W6763	
	SH-2	20mm	10x75cm	5 white 5 green					W10B62	
	SH	26mm	75cm	green			W6831	W6832		
	SH	26mm	90cm 100cm	green green				W6552	W6767	
	MH-1	31mm	75cm	green				W931	W932	W975 X31027

⊙ 1/2 circle Taper Point (heavier wire diameters)				6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
	XLH	70mm	75cm	green						W6191









ETHIBOND* *EXCEL*

Polybutylate Coated Braided Polyester Suture

Needle length and description	Length	Colour	Gauge						
			6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
⊙ J Needle Taper Point									
 <p>ASH-30</p> <p style="text-align: right;">31mm</p>	75cm	green							W969
▼ 3/8 circle TAPERCUT*			6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 <p>V-4</p> <p style="text-align: right;">17mm</p>	75cm	white				W6923			
 <p>V-26</p> <p style="text-align: right;">26mm</p>	45cm 90cm	white green			W6995		W6997		
▼ 1/2 circle TAPERCUT*			6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 <p>V-5</p> <p style="text-align: right;">17mm</p> <p>firm pledget 3mm x 3mm x 1.5mm</p>	10x75cm	5 white 5 green					W10B54		
 <p>V-5</p> <p style="text-align: right;">17mm</p> <p>firm pledget 6mm x 3mm x 1.5mm</p>	10x75cm	5 white 5 green					W10B55		
 <p>V-5</p> <p style="text-align: right;">17mm</p> <p>firm pledget 6mm x 3mm x 1.5mm</p>	10x75cm	5 white 5 green					W10B52		
 <p>V-5</p> <p style="text-align: right;">17mm</p>	90cm 90cm	white green		W6934	W6915 W6935	W6936	W6917 W6937		
 <p>V-5</p> <p style="text-align: right;">17mm</p> <p>firm pledget 6mm x 3mm x 1.5mm</p>	4x90cm	green					W4B37		
 <p>V-5</p> <p style="text-align: right;">17mm</p>	4x90cm	green					W6937M		




ETHIBOND* *EXCEL*



Polybutylate Coated Braided Polyester Suture

Needle length and description	Length	Colour	Gauge						
▼ 1/2 circle TAPERCUT*			6-0 0.7	5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 26mm 10x75cm 5 white 5 green firm pledget 6mm x 3mm x 1.5mm								W10B77	
 26mm 10x75cm 5 white 5 green								W10B72	
 26mm 90cm green firm pledget 6mm x 3mm x 1.5mm								W6977P	
 26mm 90cm 90cm white green						W6976	W6987 W6977	W6978	
 26mm 4x90cm green firm pledget 6mm x 3mm x 1.5mm								W4B77	
 26mm 4x90cm green								W6977M	
 36mm 90cm green								W6952	
 48mm 75cm green								W979	

ETHIBOND* *EXCEL*


Polybutylate Coated Braided Polyester Suture



Needle length and description	Length	Colour	Gauge				
▼ 1/2 circle TAPERCUT* (Heavy)			2-0 3	1 4	2 5	4 6	5 7
 V-37	40mm	75cm	green			869G	
 V-39	45mm	4x75cm	green			W4843	
 V-55	55mm	75cm 4x75cm	green green				BE3294 W4846


Needle length and description	Length	Colour	Gauge				
▼ 1/2 circle Reverse Cutting			4-0 1.5	2-0 3	0 3.5	1 4	2 5
 OS-4	22mm	75cm	green			6517H	6518H
 OS-4	22mm	90cm	green				W6748


ETHIBOND* EXCEL

Polybutylate Coated Braided Polyester Suture


Needle length and description	Length	Colour	Gauge				
▼ 3/8 circle Reverse Cutting - PRIME* Needle			4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 PS-2 19mm	45cm	green	W6582				


▲ 3/8 circle Conventional Cutting (Hand Held)			4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 CKP-3 90mm with 40mm retention tubing	2x50cm	green					W2991
 CKP-3 90mm	100cm	green			W993		W998


▼ 1/2 circle Reverse Cutting			4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 X-1 22mm	75cm	green			EH7679H		


▼ Straight Cutting			4-0 1.5	3-0 2	2-0 3	0 3.5	1 4
 KS 60mm	75cm	green			W623		

Needle length and description	Length	Colour	Gauge				
▼ 1/4 circle SPATULATED			5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5
 S-14 8mm	45cm 45cm	white green	W893 W894	W882			

▼ 1/2 circle SPATULATED			5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5
 S-22 8mm	45cm 45cm	white green	W883 W884				

⊙ 5/8 circle TAPERCUT*			5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5
 UV-10 10mm	23cm	white	W885				

Needle length and description	Length	Colour	Gauge				
⊙ Ski Needle Point			5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5
 SKI-22 VISI-BLACK* 22mm	20cm	white				E6102S	

⊙ Straight Point			5-0 1	4-0 1.5	3-0 2	2-0 3	0 3.5
 ST-3 22mm	107cm	green					EX10C

ETHIBOND* *EXCEL*

Polybutylate Coated Braided Polyester Suture

Ligatures and Non-needled Sutures

1.8m lengths

Gauge		green 1.8m lengths 12 sachets per box
1	4	W6155
2	5	W6156

SUTUPAK* Pre-cut Sutures

Gauge		green 13 x 60cm lengths 12 sachets per box
3-0	2	W6232
2-0	3	W6233
0	3.5	W6234