



Thermo Scientific Niton Portable XRF Analyzers



Rapid, precise metal alloy identification
for maximum performance and productivity

Thermo
SCIENTIFIC

Superior accuracy. Comprehensive analysis.

Purpose-built for the most rugged conditions, Thermo Scientific™ Niton™ XRF analyzers are easy to use and offer superior detection limits and exceptionally fast measurement times to ensure confident decision making. Get lab-quality results in the field or factory in virtually any weather conditions. Samples always remain intact and undamaged by testing.



Analyze nearly every element of interest in virtually all types of metal alloys, from tramp elements to pure metals, and everything in between. With point-and-shoot simplicity, you can view the alloy grade and chemistry on the built-in, color, touch-screen display.

WiFi, Bluetooth™ wireless and USB communications enhance data management and let you set user permissions, print certificates of analysis to document results, or operate the analyzer from your PC.

Our patented Engine Guard™ protects the detector, tube and other internal components from sharp objects that can cause damage and result in costly repairs.

This all adds up to maximum performance and increased productivity.



Which analyzer is best for your application?

Niton XRF analyzers are built for rugged use and return rapid lab-quality results



	XL2	XL2 GOLDD	XL3t	XL3t GOLDD+	XL5
Market					
Scrap Metal Recycling	✓	✓		✓	✓
Positive Material ID (PMI)			✓	✓	✓
Fabrication-Mfg/QA&QC	✓	✓	✓	✓	✓
Description	<ul style="list-style-type: none"> • Ideal for asset recovery and traceability • Analyzes up to 25 elements • Verifies incoming, in-stock or in-service material 	<ul style="list-style-type: none"> • Improved sorting speeds • Rapid results for tramp/trace element analysis • High performance and light element analysis (Mg-S) for Al and specialty alloys without helium purge or vacuum 	<ul style="list-style-type: none"> • Extended element range • Optional CCD camera and WeldSpot small spot feature for comprehensive weld analysis and component inspection 	<ul style="list-style-type: none"> • Detects and measures trace elements for FAC modeling (Cr, Cu, Mo) • Analyzes component for residual elements in HF alkylation (API RP-578) and low Si sulfidation (API RP-939-C) systems 	<ul style="list-style-type: none"> • Fastest, lightest, most powerful Niton XRF analyzer • Closer x-ray source and detector enable lower limits of detection • Provides expanded use in measuring scale, sludge, oil, powders and slurries • Enables testing in tight spots • Extended field use with hot, swappable battery • Swiping functionality
Weight	3.5 lb (1.6 kg)	3.5 lb (1.6 kg)	3.5 lb (1.6 kg)	3.5 lb (1.6 kg)	2.8 lb (1.3 kg)
X-Ray Tube Power Heavy element detection (Ba, Sb, Pb, Sn, Cd)	45kV – 2W	45kV – 2W	50kV – 2W	50kV – 2W	50kV – 5W
Detector Technology Improving light element analysis (Mg-S) / overall performance	Si-PIN	SDD	Si-PIN	SDD Ultra SDD	SDD
Communication	BT, USB	BT, USB	BT, USB	BT, USB	WiFi, BT, USB
Design/Features Tilt-screen display, hot swap, GPS, SW			Tilt screen, GPS	Tilt screen, GPS	Tilt screen, GPS, Hot swap battery
Camera/Display Identify textures, store image with analytical results, macro camera	Micro	Micro	Micro	Micro	Micro + Macro
Small Spot Sample Positioning Isolate welds and very small samples	Weld mask	Weld mask	3mm collimator	3mm collimator	3mm collimator

Scrap

Identify and sort recycled metals quickly and with accuracy

Incorrect material sorting results in lost time and disrupts daily operations. Thermo Scientific™ Niton™ XRF analyzers are engineered to provide the industry with faster sorting and more accurate results. Testing time is almost instantaneous for routine scrap, and just a few seconds longer to obtain lab-quality chemistry. Our smart and ever-evolving alloy grade library sorts alloys with improved accuracy. Rugged with sealed construction, analyzers are dust- and waterproof for worry-free use virtually anywhere. Niton XRF analyzers are the perfect fit for metal recycling companies.



Fabrication and Manufacturing

Take control of material verification and accuracy

The verification of metal alloys for manufacturing quality assurance and quality control has never been more important to satisfy product reliability and safety standards. From metal production to service centers and distributors, component fabrication to final product assembly, the potential for material mix-ups is very real, and the need for traceability is a top priority. Niton XRF analyzers deliver fast, accurate elemental analysis and positive identification for manufacturing requirements:



- Components
- Wire strands as fine as 1 mm
- Rods
- Finished welds
- Bolts, rivets, and other fasteners
- Complete fabricated assemblies

Positive Material Identification

Verify the integrity of your process systems

For oil and gas refineries, petrochemical plants, and power generation industries, the emphasis on safety and accident prevention is critical. Positive identification ensures the integrity of your materials and systems throughout your enterprise:



- Rods and wire strands
- Finished welds and weld beads
- Bolts, rivets, and other fasteners
- Valves and flanges
- Complete reaction vessels

Rely on Niton XRF analyzers to ensure operational safety and maintain regulatory compliance.

Families of alloys that can be accurately analyzed with a Niton XL2 Series or XL3t Series include:

- Stainless steels
- Nickel (Ni) alloys
- Cobalt (Co) alloys
- Ni/Co alloys
- Tool steels
- Chromium-molybdenum (Cr-Mo) steels
- Exotic alloys of most types (alloys of tantalum, hafnium and tungsten)
- Copper (Cu) alloys
- Titanium (Ti) alloys
- Wrought aluminum (Al) alloys
- Low alloy steels
- Zirconium (Zr) alloys

In addition, the Niton XL5 XRF analyzer provides improved limits of detection for light element analysis:

- Silicon
- Aluminum
- Sulfur
- Magnesium
- Phosphorous



Thermo Scientific™ GOLDD™ technology brings true lab-quality performance to handheld XRF analyzers. Delivering up to 10x faster measurement times than conventional technologies, it also provides the highest sensitivity and measurement accuracy, plus the capability of measuring light elements without helium purge or vacuum.

Thermo Scientific Niton XL5 Portable XRF Analyzer

Introducing Niton XL5. At 2.8 lbs. (1.3 kg.), Niton XL5 is the lightest XRF metals analyzer available. Light weight reduces operator fatigue in verifying alloy composition and grade. A macro-camera captures a simple image. A micro-camera ensures precise sample analysis location.



The Future is in Your Hands

Outstanding Service and Support

Superior XRF analysis solutions, backed by our worldwide sales and service

Thermo Scientific is recognized as the leader in XRF analysis technology, serving companies in more than 75 countries on six continents. We serve our customers through corporate resources and a dedicated network of more than 70 distributors and 30 factory-trained service centers around the world to provide the most effective customer service possible. Our global reach and resources not only ensure worry-free product support, we also offer comprehensive services including application consulting and training anywhere you need them.



www.thermoscientific.com/portableID

Bluetooth is a registered trademark of Bluetooth SIG.

© 2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Americas

Boston, MA
+1 978 670 7460
niton@thermofisher.com

Europe, Middle East, Africa

Munich, Germany
+49 89 3681 380
niton.eur@thermofisher.com

India

Mumbai, India
+91 22 6680 3000
info@thermofisher.com

Asia Pacific

New Territories, Hong Kong
+852 2885 4613
niton.asia@thermofisher.com

Thermo
SCIENTIFIC

A Thermo Fisher Scientific Brand